

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 磷铜, 镍底30u"MIN, 表面镀金0.8u"MIN

Contact: Phosphorous, 0.8u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C

Ordering Information

F243-11 08 A0 C MU B 2

NO. OF PINS
PER ROW
2-40P

Contact Plating

Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

INSULATOR

MATERIAL:

B: PA6T

C: PA9T

D: LCP

B3=2U"

B4=3U"

B5=5U"

B6=10U"

B7=15U"

B8=20U"

B9=30U"

PACKING

A: PE Bag

B: Tape & Reel





C: Tube

D: Tube+CAP

E: Tray

TYPE1:1

TYPE2:2



RoHS
COMPLIANT

客编: V1169

注意
事项

- 带*为品质重点检验尺寸.
- 端子材质为磷铜.



| | | | | | | | | | | |
|-----|------|--------|--------------------------|-------|-------|---------|--------|----------------|---|---|
| | | | OPERATION | | SCALE | | Fit | | Yxcon 东莞市宇熙精密连接器有限公司 | |
| | | | X.X | ±0.25 | UNIT | | MM | | www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd. | |
| | | | X.XX | ±0.20 | SIZE | A4 | DESIGN | 秦星宇 2020.06.19 | PART NO. | F243-1108A0CMUB2 |
| | | | X.XXX | ±0.10 | SHEET | 1/1 | CHECK | 谭志华 | TITLE: | FH2.0*4.3 1*8P SMT 反脚位 展宽4.1 PA9T料 磷铜 镀普金 无cap+900卷 V1169 |
| | | | Angle | ±3° | PROJ. | APPROVE | 6.24 | Customer No. | | |
| REV | DATE | SYMBOL | MODIFICATION DESCRIPTION | | DIM | TOL | | | | |