




**SPECIFICATIONS**

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material:Nylo66,UL94V-0



Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-1.25-2Y	1.25	4.25
3	HC-1.25-3Y	2.50	5.50
4	HC-1.25-4Y	3.75	6.75
5	HC-1.25-5Y	5.00	8.00
6	HC-1.25-6Y	6.25	9.25
7	HC-1.25-7Y	7.50	10.50
8	HC-1.25-8Y	8.75	11.75
9	HC-1.25-9Y	10.00	13.00
10	HC-1.25-10Y	11.25	14.25
11	HC-1.25-11Y	12.50	15.50
12	HC-1.25-12Y	13.75	16.75
13	HC-1.25-13Y	15.00	18.00
14	HC-1.25-14Y	16.25	19.25
15	HC-1.25-15Y	17.50	20.50
16	HC-1.25-16Y	18.75	21.75

			GENERL TOLERANCE		制 图 DRAWING		 <b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	1.25 孔座	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	HC-1.25-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1