




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2011.03.29	蒙華明



Specifications
 Current Rating: 2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn requirement for environment protection.




Ordering Information

C SFB102 - XX XX A 001 C 1 A X

No. of Pins per Row
 02~40
 Standard Plating
 02=Gold Flash
 Selective Plating
 01=Tin
 05=Gold Flash/Tin

Color
 1=Black
 Standard Packing
 A=Box
 Selective Packing
 C=Tube

Recommended P.C.Board
 Layout
 (Tolerance:±0.05)



格 菱 股 份 有 限 公 司 Greenconn Corporation				GENERAL TOLERANCE X.±5.0° X.±3.0° .XX±2.0° .XXX±1.0°		DESIGN: 蒙華明 CHECKED: 劉北平 AUDITED: 李 輝 APPROVED: cc_li		DWG. NO. CSFB102-CA1CA		TITLE. 2.00 FEMALE HEADER SINGLE ROW RHGT ANGLE SERIES	
REV. 01	UNIT. mm	SCALE. 5:1	PAGE. 1/1	X.±0.30 X±0.25 .XX±0.15 .XXX±0.10		DATE: 2011.03.29 DATE: 2011.03.29 DATE: 2011.03.29 DATE: 2011.03.29		PART NO. CSFB102-XXXX A001C1AX			

