



**SPECIFICATIONS**

- 1、Current Rating: 6A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500 AC/minute
- 7、Material:Housing:Nylon66,UL94V-0



Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-3.96-2Y	3.96	8.80
3	HC-3.96-3Y	7.92	12.76
4	HC-3.96-4Y	11.88	16.72
5	HC-3.96-5Y	15.84	20.68
6	HC-3.96-6Y	19.80	24.64
7	HC-3.96-7Y	23.76	28.60
8	HC-3.96-8Y	27.72	32.56
9	HC-3.96-9Y	31.68	36.52
10	HC-3.96-10Y	35.64	40.48

			GENERAL TOLERANCE	制图 DRAWING	 <b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	3.96 孔座	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-3.96-NY	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°					
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						