


SPECIFICATION

Insulator: PBT+G. F. (UL94V-0)

RoHS Compliant



Contact Quantit	Dimensions
	D
10	0.95 [24.1]
14	1.15 [29.2]
16	1.25 [31.8]
20	1.45 [36.8]
26	1.75 [44.5]
34	2.15 [54.6]
40	2.45 [62.2]
50	2.95 [74.9]
60	3.45 [87.6]
64	3.65 [92.7]

Order Information

E C xx SR BK

E=2.54mm FEMALE EDGE SLOT

C=IDC TYPE

NO. OF PINS: 10~64

SR=Strain Relief

BK=Black
GY=Gery
BU=Blue

WingTAT®

深圳市格林柏电子技术开发有限公司

X. ± 0.30	APPD:	PART NO: ECxxSRBK
.X ± 0.20	CHKD: HZF	
.XX ± 0.10	DR:	
.XXX ± 0.05		
X° ± 1°		DWG NO:
.X° ± 0.5°		SCALE: 1:1
UNITS: mm		SHEET: 10F1
		REV: A

REV	ECN NO	DESCRIPTION	DATE
A			