

3D图示 (参考)




■ Specifications.

- Voltage rating: 250V AC/DC
- Current rating: 5A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25 °C ~ +85 °C
- Insulation resistance: 1000mΩ Min
- Contact resistance: 20mΩ Max
- Material: Nylon66 UL94V-0

X5080 H -XX- N0

① ② ③ ④

- ① Series No.
- ② Category : H-HSG
- ③ Row No.Pin No.XX-02-12
- ④ Material: N0-Nylon66 94V-0



POLES	A	B
2	5.08	10.16
3	10.16	15.24
4	15.24	20.32
5	20.32	25.40
6	25.40	30.48
7	30.48	35.56
8	35.56	40.64
9	40.64	45.72
10	45.72	50.80
11	50.80	55.88
12	55.88	60.96

X5080H-XX-NO	Nylon66 UL 94V-0	X5080T	X5080W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

广东星坤科技股份有限公司

生 日期  
效 日期  
△×  
△×  
△×

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	5.08mm Crimp Style Connectors
CHKD	UNIT: mm/in	PART NO.: X5080H-XX-N0
APPD	SIZE: A4	DWG NO.: X-X5080H-XX-N0
		WEIGHT SHEET REVISION
		1/1 A0