



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperature Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltage: 1000V AC/minute
- 7、Material: Nylon66 UL94-V0

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XH-2Y	2.50	7.50
3	HC-XH-3Y	5.00	10.00
4	HC-XH-4Y	7.50	12.50
5	HC-XH-5Y	10.00	15.00
6	HC-XH-6Y	12.50	17.50
7	HC-XH-7Y	15.00	20.00
8	HC-XH-8Y	17.50	22.50
9	HC-XH-9Y	20.00	25.00
10	HC-XH-10Y	22.50	27.50
11	HC-XH-11Y	25.00	30.00
12	HC-XH-12Y	27.50	32.50
13	HC-XH-13Y	30.00	35.00
14	HC-XH-14Y	32.50	37.50
15	HC-XH-15Y	35.00	40.00
16	HC-XH-16Y	37.50	42.50

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	XH(TJC3) 孔座	版本 REV.	A
1			初版发行		比例 SCALE		产品料号 PART NO.	HC-XH-NY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°		投影 Projection		材料 MATERIAL		页次 SHEET	1/1