



■ 技术参数 SPECIFICATIONS:

- ◆ 线数: 2~12
- ◆ Poles: 2~12
- ◆ 适用线规: AWG #30~#24
- ◆ Applicable Wire: AWG #30~#24
- ◆ 额定电压: 250V DC/AC
- ◆ Voltage Rating: 250V DC/AC
- ◆ 额定电流: 2.0A
- ◆ Current Rating: 2.0A
- ◆ 耐压: 800V AC
- ◆ Withstand Voltage: 800V AC
- ◆ 温度范围: -25°C~+85°C
- ◆ Working Temperature: -25°C~+85°C
- ◆ 绝缘电阻: ≥1000MΩ
- ◆ Insulation Resistance: 1000MΩ (MIN)
- ◆ 接触电阻: ≤20mΩ
- ◆ Contact Resistance: 20mΩ (MAX)
- ◆ 材质/颜色: 尼龙66 UL 94V-0 本色
- ◆ Material: Nylon 66 UL 94V-0 Color Nature

线数 Circuits	Dim.A	Dim.B	Dim.C
2	2.0	4.5	5.8
3	4.0	6.5	7.8
4	6.0	8.5	9.8
5	8.0	10.5	11.8
6	10.0	12.5	13.8
7	12.0	14.5	15.8
8	14.0	16.5	17.8
9	16.0	18.5	19.8
10	18.0	20.5	21.8
11	20.0	22.5	23.8
12	22.0	24.5	25.8

APPROVALS		DATE	PART NO.		SCALE	SHEET
DRAWN	G.M.Chen	2015/7/17	A2001-XXP		1:1	1 OF 1
CHECKED						
APPROVALS						
<p style="text-align: center;"><b>DEALON 德之隆</b> ELECTRONICS CO.,LTD</p>						
<p style="text-align: center;">TITLE: 2.0mm Crimp Style Connectors</p>						
<p style="text-align: center;">PART NO. A2001-XXP</p>						
<p style="text-align: center;">UNIT: mm SCALE: 1:1 SHEET 1 OF 1</p>						
<p style="text-align: center;">DRAWING NO. PROJ. </p>						
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS ARE

30~40L ±	±0.30	ANGLE	
10~30	±0.20		
5~10	±0.15	±2°	
~5	±0.10		