



■ 技术参数 SPECIFICATIONS:

- ◆ 线数: 4~40
- ◆ Poles: 4~40
- ◆ 适用线规: AWG #28~#22
- ◆ Applicable Wire: AWG #28~#22
- ◆ 额定电压: 250V DC/AC
- ◆ Voltage Rating: 250V DC/AC
- ◆ 额定电流: 3.0A
- ◆ Current Rating: 3.0A
- ◆ 耐压: 1000V AC
- ◆ Withstand Voltage: 1000V AC
- ◆ 温度范围: -25°C~+85°C
- ◆ Working Temperature: -25°C~+85°C
- ◆ 绝缘电阻: $\geq 1000M\Omega$
- ◆ Insulation Resistance: 1000MΩ (MIN)
- ◆ 接触电阻: $\leq 20m\Omega$
- ◆ Contact Resistance: 20mΩ (MAX)
- ◆ 材质/颜色: 尼龙 94V-0 本色
- ◆ Material: Nylon UL 94V-0 Color Nature
- ◆ 包装数量: 1000 pcs
- ◆ Packaging Quantity: 1000 pcs

线数 Circuits	尺寸			线数 Circuits	尺寸		
	Dim.A	Dim.B	Dim.C		Dim.A	Dim.B	Dim.C
4	2.0	4.5	6.0	20	18.0	20.5	22.0
6	4.0	6.5	8.0	22	20.0	22.5	24.0
8	6.0	8.5	10.0	24	22.0	24.5	26.0
10	8.0	10.5	12.0	26	24.0	26.5	28.0
12	10.0	12.5	14.0	28	26.0	28.5	30.0
14	12.0	14.5	16.0	30	28.0	30.5	32.0
16	14.0	16.5	18.0	—	—	—	—
18	16.0	18.5	20.0	40	38.0	40.5	42.0

ECN NO.		REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
		A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/7/17
CHECKED		
APPROVALS		

TOLERANCES ARE		30~40L ±0.30	40~50 ±0.20	50~100 ±0.15	100~500 ±0.10	500~1000 ±0.10
ANGLE		±2°				
PART NO.	A2005-XXP		UNIT:	mm	SCALE:	1:1
TITLE:	2.0mm Crimp Style Connectors		DRAWING NO.		SHEET	1 OF 1
DEALON 德之隆®		ELECTRONICS CO.,LTD		PROJ.		