


.XX ±0.13 .XXX ±0.10




NOTES:

MATERIAL:

HOUSING:BLUE THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, NICKEL PLATEDCONTACT:COPPER ALLOY, GOLD FLASH PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

628 SERIES D-SUB CONNECTOR			SW REFERENCE NO.: 628M ASSEMBLY			
			DRAWN: C.B		DATE: AUG. 01/2018	
			CHECKED:		DATE:	
	EDAC INC TORONTO, ONTARIO CANADA TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1		SHEET 1 OF	1
			DRAWING NUMBER: 628-M37-221-LN1		ISSUE	
YOUR CONNECTION			PART NUMBER:	ART NUMBER: 628-M37-221-LN1		1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.