



TOLERANCE UNLESS OTHERWISE SPECIFIED		
.X	±0.25	
.XX	±0.13	
.XXX	±0.10	

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL 1







MATERIAL:

HOUSING: BLACK THERMOPLASTIC POLYESTER, UL94V-0

SHELL: STEEL, NICKEL PLATED

CONTACT: COPPER ALLOY,  $15\mu$  GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT

CONTACT RESISTANCE:  $25m\Omega$  MAX. INSULATOR RESISTANCE:  $5000M\Omega$  min.

**DIELECTRIC** 


WITHSTANDING VOLTAGE: 1000V AC rms

PART NUMBER:



0.80

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.





THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

	SW REFERENCE NO.: 628M ASSEMBLY		
	DRAWN: C.B	DATE: AUG. 01/20	018
	CHECKED:	DATE:	
TIONS AND OPIED	SCALE: 1:1	SHEET 1 OF	1
	DRAWING NUMBER: 628-M37-321-BN1		ISSUE
PATUS			

628-M37-321-BN1