




.XX ±0.13














NOTES:

MATERIAL:

HOUSING:GREEN THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, TIN PLATEDCONTACT:COPPER ALLOY, 15µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

			SW REFERENCE NO.: 628M ASSEMBLY		
	628 SERIES D-SUB (ONNECTOR	DRAWN: C.B	DATE: AUG. 01/20)18
			CHECKED:	DATE:	
	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND	SCALE: 1:1	SHEET 1 OF	1
	YOUR CONNECTION TO QUALITY & SERVICE	SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 628-M09-321-GT6		ISSUE
			PART NUMBER: 628-M09	-321-GT6	1



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.