


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



NOTES:

MATERIAL: HOUSING: DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT **INSERTION FORCE:** WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: **10A PER CONTACT** CONTACT RESISTANCE: 10mΩ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 541-Wire Wrap .026x.024(0.66x0.61) - Tail LG.=.620(15.75)

	415 & 438 SERIES CARD EDGE		SW REFERENCE NO.: 415 ASSEMBLY		
			DRAWN: W.T	DATE: AUG. 01/20)18
			CHECKED:	DATE:	
ORMS TO RECTIVES MPLIANCY.	EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1
			DRAWING NUMBER: 415-029-541-222		ISSUE
			PART NUMBER: 415-029-	541-222	1



THIS SERIES FULLY CONFOR THE EUROPEAN UNION DIRI 2011/65/EU FOR RoHS COMF