



DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT INSERTION FORCE: WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: **10A PER CONTACT** CONTACT RESISTANCE: $10m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 542-Wire Wrap .050x.025(1.27x0.61) - Tail LG.=.790(20.07)

	415 & 438 SERIES CARD EDGE		SW REFERENCE NO.: 415 ASSEMBLY		
			DRAWN: W.T	DATE: AUG. 01/20	018
			CHECKED:	DATE:	
RMS TO	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND	SCALE: 1:1	SHEET 1 OF	1
ECTIVES PLIANCY.	EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE	SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 415-023-542-222		ISSUE
			PART NUMBER: 415-023-	542-222	1



THIS SERIES FULLY CONFORM THE EUROPEAN UNION DIREC 2011/65/EU FOR RoHS COMPL

SW REFERENCE NO.: 415 ASSEMBLY				
DRAWN: W.T	DATE: AUG. 01/2018			
CHECKED:	DATE:			
SCALE: 1:1	SHEET 1 OF 1			
DRAWING NUMBER: 415-023-5	542-222 ISSUE			
PART NUMBER: 415-023-5	542-222 1			