


REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28	瞿寿坤	胡海萍	胡海萍

REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28	瞿寿坤	胡海萍	胡海萍

REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28	瞿寿坤	胡海萍	胡海萍

15P	40	38.6	35
14P	37.5	36.1	32.5
13P	35	33.6	30
12P	32.5	31.1	27.5
11P	30	28.6	25
10P	27.5	26.1	22.5
9P	25	23.6	20
8P	22.5	21.1	17.5
7P	20	18.6	15
6P	17.5	16.1	12.5
5P	15	13.6	10
4P	12.5	11.1	7.5
3P	10	8.6	5
2P	7.5	6.1	2.5
NUMBER OF PINS		DIM.A	DIM.B
		DIM.A	DIM.C



适应基板厚度: 1.2mm~1.6mm  
 温度范围: -25°C~85°C  
 额定电压: 250V AC/DC  
 额定电流: 3A  
 接触电阻: ≤0.01Ω  
 绝缘电阻: ≥1000MΩ  
 耐压: 1000V AC/minute

技术要求:  
 1) 材质:见附表;  
 2) 电镀:见附表;  
 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;  
 4) 端子表面无氧化、电镀不良等现象。

DIM	TOL	DIM	DEC
X.	X°	X°	+3.00°
X.X	+0.15	X.X°	+2.00°
X.XX	+0.25	X.XX°	+1.00°
X.XXX	+0.15	X.XXX°	

2	PIN	n PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:白色
NO.	NAME	Q' TY	DESCRIPTION

DRAW :	瞿寿坤	2020-8-28	TITLE: WAFER 2. 5XHBWA 卧式 DIP	DRAW NAME:	HC-XHB-4A-TW
DESIGN:	瞿寿坤	2020-8-28	SERIES: 1501 SERIES	DRAW NO.	
CHECK:	胡海萍	2020-8-28	P/N:	UNIT:	mm
APPROVED	胡海萍	2020-8-28	REV. 1.00	SCALE	N/A
CUSTOMER DRAWING					

深圳市虹成电子有限公司					
DESCRIPTION					

