




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28	瞿寿坤	胡海萍	胡海萍

REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED

NUMBER OF PINS	DIM.A	DIM.B	DIM.C
15P	40	38.6	35
14P	37.5	36.1	32.5
13P	35	33.6	30
12P	32.5	31.1	27.5
11P	30	28.6	25
10P	27.5	26.1	22.5
9P	25	23.6	20
8P	22.5	21.1	17.5
7P	20	18.6	15
6P	17.5	16.1	12.5
5P	15	13.6	10
4P	12.5	11.1	7.5
3P	10	8.6	5
2P	7.5	6.1	2.5



PCB LAYOUT

2PIN

适应基板厚度: 1.2mm~1.6mm
 温度范围: -25°C~85°C
 额定电压: 250V AC/DC
 额定电流: 3A
 接触电阻: ≤0.01Ω
 绝缘电阻: ≥100MΩ
 耐压: 1000V AC/minute

- 技术要求:
- 1) 材质:见附表;
 - 2) 电镀:见附表;
 - 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
 - 4) 端子表面无氧化、电镀不良等现象。

NO.	PIN	n	PCS	DESCRIPTION
2	Housing	1	PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	NAME	Q/ TY		材质:PA66,颜色:本色

GENERAL TOLERANCES			
DIM	TOL	DIM	DEC
X.	X°	X°	±3.00°
X.X	±0.15	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

DRAW :	DESIGN :	CHECK :	APPROVED :	CUSTOMER DRAWING	SCALE	N/A
瞿寿坤	瞿寿坤	胡海萍	胡海萍		1:1.00	
TITLE: WAFER 2. 5XHBWA 卧式 DIP				DRAW NAME: HC-XHB-5AW-M		
SERIES: 1501 SERIES				DRAW NO.		
P/N:				UNIT: mm		
REV. 1.00				SHEET: 1/1		

深圳市虹成电子有限公司