


REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28	瞿寿坤	胡海萍	胡海萍

NO.	PIN	n	PCS	DESCRIPTION
2				材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1	PCS	材质:PA66 (UL94V-0),颜色:本色

NO.	NAME	QTY	DESCRIPTION
-----	------	-----	-------------

NUMBER OF PINS	DIM.A	DIM.B	DIM.C
15P	40	38.6	35
14P	37.5	36.1	32.5
13P	35	33.6	30
12P	32.5	31.1	27.5
11P	30	28.6	25
10P	27.5	26.1	22.5
9P	25	23.6	20
8P	22.5	21.1	17.5
7P	20	18.6	15
6P	17.5	16.1	12.5
5P	15	13.6	10
4P	12.5	11.1	7.5
3P	10	8.6	5
2P	7.5	6.1	2.5



GENERAL TOLERANCES	DIM	TOL	DIM	DEC
X.	X°	±3.00°		
X.X	X.X°	±2.00°		
X.XX	X.XX°	±1.00°		
X.XXX	X.XXX°	±0.15°		

适应基板厚度: 1.2mm~1.6mm
 温度范围: -25°C~85°C
 额定电压: 250V AC/DC
 额定电流: 3A
 接触电阻: ≤0.01Ω
 绝缘电阻: ≥1000MΩ
 耐压: 1000V AC/minute

技术要求:
 1) 材质:见附表;
 2) 电镀:见附表;
 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
 4) 端子表面无氧化、电镀不良等现象。

深圳市虹成电子有限公司

TITLE: WAFER 2.5XHBWA 卧式 DIP
 SERIES: 1501 SERIES
 P/N:
 REV. 1.00 SCALE N/A

DRAW : 瞿寿坤 2020-8-28
 DESIGN: 瞿寿坤 2020-8-28
 CHECK: 胡海萍 2020-8-28
 APPROVED: 胡海萍 2020-8-28

CUSTOMER DRAWING
 DRAW NAME: HC-XHB-6A-M
 DRAW NO.
 UNIT: mm 1/1

材质:黄铜,电镀:镀亮锡60u"MIN
 材质:PA66 (UL94V-0),颜色:本色

DESCRIPTON

2020-8-28

2020-8-28

2020-8-28

2020-8-28

1.00

N/A

1/1

1/1

1/1

1/1

1/1

1/1

1/1

1/1

1/1

PCB LAYOUT