




SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: WaferPA66, UL94V-0
PIN Brass Tin-plated




PCB LAYOUT

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-PA-02A	2.00	6.00
3	HC-PA-03A	4.00	8.00
4	HC-PA-04A	6.00	10.00
5	HC-PA-05A	8.00	12.00
6	HC-PA-06A	10.00	14.00
7	HC-PA-07A	12.00	16.00
8	HC-PA-08A	14.00	18.00
9	HC-PA-09A	16.00	20.00
10	HC-PA-10A	18.00	22.00
11	HC-PA-11A	20.00	24.00
12	HC-PA-12A	22.00	26.00



7~9A



10~16A

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	直针	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-PA-NA	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						