

- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C ~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XHB-2AW-X	2.50	7.50
3	HC-XHB-3AW-X	5.00	10.00
4	HC-XHB-4AW-X	7.50	12.50
5	HC-XHB-5AW-X	10.00	15.00
6	HC-XHB-6AW-X	12.50	17.50
7	HC-XHB-7AW-X	15.00	20.00
8	HC-XHB-8AW-X	17.50	22.50
9	HC-XHB-9AW-X	20.00	25.00
10	HC-XHB-10AW-X	22.50	27.50
11	HC-XHB-11AW-X	25.00	30.00
12	HC-XHB-12AW-X	27.50	32.50
13	HC-XHB-13AW-X	30.00	35.00
14	HC-XHB-14AW-X	32.50	37.50
15	HC-XHB-15AW-X	35.00	40.00
16	HC-XHB-16AW-X	37.50	42.50

Ordering Information

HC-XHB - N*** - *

Pin Type Colour


A: 直针 蓝色

AW: 弯针 黄色

Y: 黄色

F: 红色

W: 白色



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK		产品名称 TITLE	XHB (2.50) 弯针	版本 REV.	A
			X.X	±0.30	批准 APPROVAL		产品料号 PART NO.	HC-XHB-NAW-X	单位 UNITS	mm
1	初版发行		X.XX	±0.20	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection					
			Angle	±3.0°						