



Specifications:

规格:

- Voltage rating: 250V AC/DC
额定电压: 250V AC/DC
- Current rating: 1A AC/DC
额定电流: 1A AC/DC
- Withstanding voltage: 500V AC/minute
耐受电压: 500V AC/分钟
- Temperature range: -40°C~+105°C
温度范围: -40°C~+105°C
- Insulation resistance: 1000MΩ min
绝缘电阻: 1000MΩ Min
- Contact resistance: 20mΩ Max
接触电阻: 20mΩ Max

X2001 W V S - 2xXX D - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: V-Straight 180°
4. Welding Way: S-SMT
5. Row No. Pin No.: 2xXX-2x03-2x30P
6. Category: D-Short ears
7. Material: 6T-Nylon 6T UL 94V-0
8. Plating: V01-Gold Flash

Poles	Dimensions		Poles	Dimensions	
	A	B		A	B
2x03	4.00	21.60	2x13	24.00	41.60
2x04	6.00	23.60	2x15	28.00	45.60
2x05	8.00	25.60	2x17	32.00	49.60
2x06	10.00	27.60	2x20	38.00	55.60
2x07	12.00	29.60	2x22	42.00	59.60
2x08	14.00	31.60	2x25	48.00	65.60
2x10	18.00	35.60	2x30	58.00	75.60
2x12	22.00	39.60	/		

X2001WWS-2xXXD-6TV01	Nylon 6T	Brass	X2001H
PART NO	Material	Material(Pin)	Suitable XKD IDC

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.0mm Crimp Style Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X2001WWS-2xXXD-6TV01
		DWG NO.:
		X-X2001WWS-2xXXD-6TV01
		WEIGHT
		SHEET
		REVISION
		1/1
		A0

文件工程章