
THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.

ISSUE NUMBER ORIGINAL

(1)



NOTES:


MATERIAL: HOUSING: DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT INSERTION FORCE: WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: 10A PER CONTACT CONTACT RESISTANCE: $10m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 541-Wire Wrap .026x.024(0.66x0.61) - Tail LG.=.620(15.75)

	415 & 438 SERIES CARD EDGE		SW REFERENCE NO.: 415 ASSEMBLY			
			DRAWN: W.T DATE: A		AUG. 01/2018	
			CHECKED:	DATE:		
IS TO	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND	SCALE: 1:1	SHEET 1 OF	1	
CTIVES IANCY.	YOUR CONNECTION TO QUALITY & SERVICE	SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 415-023-541-112		ISSUE	
			PART NUMBER: 415-023-	541-112	1	





THIS SERIES FULLY CONFORMS THE EUROPEAN UNION DIRECT 2011/65/EU FOR RoHS COMPLIA