

<u>Contact Dimensions:</u>
523-P.C. Tail .025 Sq.(0.64 Sq.) - Tail LG=.390(9.91)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

.330[8.38] CARD SLOT .160[4.06] POINT OF CONTACT

50 [3.81]







YOUR CONNECTION TO QUALITY & SERVICE

	NOTE HELENETOE NO. OICENO WOOLER		
	DRAWN: R.STA.MONICA	DATE:MAY.16/2017	
	CHECKED:	DATE:	
	SCALE: 1:1	SHEET 1	OF 2
)	DRAWING NUMBER		ISSUE
	0.45 5110 1446750		,

ACAD REFERENCE NO 345-ENG-MASTER

345-ENG-MASTER

INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0

CONTACT MATERIAL; COPPER TIN ALLOY

CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

SECTION A-A











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2

345-ENG-MASTER