

Contact Dimensions:

544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05)

.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing

2x \varnothing .128 3.25

6.200 157.48

6.360 161.54

6.675 169.55

A

.600 15.24
.250 6.35

A

6.935 176.15

.330 8.38 CARD SLOT
.160 4.06 POINT OF CONTACT

SECTION A-A

ACAD REFERENCE NO.

- INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0
- CONTACT MATERIAL; COPPER TIN ALLOY
- CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

TORONTO, ONTARIO