



P/N LEGEND

A2006	H-XP	N	0	X	NP	N	00	G	
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

① Series No.
 ② Connector type: H=Housing
 ③ No. of circuits
 ④ N=Halogen Free
 ⑤ Material: 0=Nylon 66-V0
 ⑥ Color: W=White B=Black
 ⑦ Plating code: NP=Non-plating
 ⑧ Plating code: N=Non-plating
 ⑨ Option code: 00=Standard,Without yellow point
 ⑩ Packing code: G=Bag

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Material: Nylon 66,UL94V-0

Circuit No.	Dimensions			
	A	B	C	D
02P	2.00	4.60	2.30	5.60
03P	4.00	6.60	2.30	7.60
04P	6.00	8.60	4.30	9.60
05P	8.00	10.60	6.50	11.60
06P	10.00	12.60	6.50	13.60
07P	12.00	14.60	6.50	15.60
08P	14.00	16.60	6.50	17.60
09P	16.00	18.60	6.50	19.60
10P	18.00	20.60	14.50	21.60
11P	20.00	22.60	14.50	23.60
12P	22.00	24.60	14.50	25.60
13P	24.00	26.60	14.50	27.60
14P	26.00	28.60	14.50	29.60
15P	28.00	30.60	14.50	31.60
16P	30.00	32.60	14.50	33.60

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.	
UNIT		SCALE	SHEET	TITLE:	
mm		1 : 1	1 of 1	2.00mm PITCH HOUSING	
DRAWN BY		APPROVED BY			
周傑亮		董正一			
2012.1.10		2012.1.10			
GENERAL TOLERANCE		ANGLE±			
A4	EN20220302965	2022.03.02	劉建芳	X. X±0.25	DRAW NO. : A2006H-XPXXXXXXX
A3	EN20200116175	2020.01.16	劉建芳	X. XX±0.15	
A2	EN1401080002	2014.01.02	郭木恩	X. XXX±0.05	
A1	EN1308090274	2013.08.12	郭木恩		
A0	NEW RELEASE	2012.1.10	周傑亮		REV. A4
REV.	DESCRIPTION	DATE	NAME		