
THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.

ORIGINAL

(1)




NOTES:

MATERIAL:HOUSING:DIALLYL PTHYHALATE, UL94V-0CONTACT MATERIAL:COPPER ALLOYCONTACT PLATING:GOLD PLATING OVER NICKELINSERTION FORCE:6 TO 16 Oz (0.56 TO 4.45N) PER CONTACTWITHDRAWAL FORCE:6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CONTACT TYPE: 520-P.C Tail .025x.024(0.64x0.61) - Tail LG.=.215(5.46)

			SW REFERENCE NO.: 415 ASSEMBLY		
			DRAWN: W.T	DATE: AUG. 01/20	018
			CHECKED:	DATE:	
o	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND	SCALE: 1:1	SHEET 1 OF	1
ÆS CY.	YOUR CONNECTION TO QUALITY & SERVICE	SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 415-017-	520-122	ISSUE
			PART NUMBER: 415-017-	520-122	1



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY