



3P



4P,5P



2P

SPECIFICATIONS

Current Rating: 9A AC,DC
 Voltage Rating: 600V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Material: Nylon 66,UL94V-2
 Color: Natural(Translucent)

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
C4255HF-02P	4.20	9.60
C4255HF-03P	8.40	13.80
C4255HF-04P	12.60	18.00
C4255HF-05P	16.80	22.20



JOINT TECH ELECTRONIC IND. CO., LTD.
 JOY DAY INDUSTRIAL CO., LTD.

UNIT: mm
 SCALE: 1 of 1
 SHEET: 1 of 1

DRAWN BY: 李勤
 2006.06.07
 APPROVED BY: 董正一
 2006.06.07

GENERAL TOLERANCE

REV.	DESCRIPTION	DATE	X. XX±0.15	ANGLE±
A1	REVISE	2007.08.23	X. X±0.25	
A0	NEW RELEASE	2006.06.07	X. XXX±0.05	

TITLE:
 4.20mm PITCH
 HOUSING-RECEPTACLE,
 SINGLE ROW, MINI-FIT

DRAW NO.: C4255HF-XP
 REV. A1