



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material:PA66,UL94V-0

孔位 Poles	尺寸 (mm)			
	A	B	C	D
2	1.25	2.00	3.75	_____
3	2.50	3.20	5.00	_____
4	3.75	4.00	6.25	_____
5	5.00	4.00	7.50	_____
6	6.25	6.25	8.75	_____
7	7.50	6.25	10.00	_____
8	8.75	6.25	11.25	8.75
9	10.00	6.25	12.50	9.75
10	11.25	8.20	13.75	11.00
11	12.50	8.20	15.00	11.00
12	13.75	8.20	16.25	11.00
13	15.00	8.20	17.50	11.00
14	16.25	8.20	18.75	11.00
15	17.50	8.20	20.00	11.00

1251H-XXP	PA66 UL94V-0	1251W	1251T
PART NO	Material	Suitable Wafer	Suitable Terminal

—		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1			
Mikey	Tom	Jerry	PART NAME	1251H-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25		
			MODEL NAME	H-1251H-XXP		X.x	±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx	±0.15
			FILE.NO.						