



SPECIFICATIONS
 Current Rating: 9A AC,DC
 Voltage Rating: 600V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Material: Nylon 66,UL94V-2
 Color: Natural(Translucent)

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
C4255HM-02P	4.20	9.60
C4255HM-03P	8.40	13.80
C4255HM-04P	12.60	18.00
C4255HM-05P	16.80	22.20

		UNIT	SCALE
		mm	1 of 1
		DRAWN BY	APPROVED BY
		李勤	董正一
		2006.06.07	2006.06.07
		GENERAL TOLERANCE	
		X. X±0.25	ANGLE±
		X. XX±0.15	
		X. XXX±0.05	
A0	NEW RELEASE	2006.06.07	TITLE: 4.20mm PITCH HOUSING-PLUG, SINGLE ROW, MINI-FIT
REV.	DESCRIPTION	DATE	
			DRAW NO. : C4255HM-XP
			REV. A0