

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃





额定电压: 250V AC/DC

额定电流: 7A

接触电阻: $\leq 0.01 \Omega$

绝缘电阻: >math>\geq 1000M\Omega</math>

耐 压: 1500V AC/minute



PCB LAYOUT

9P	31.68	35.64
8P	27.72	31.68
7P	23.76	27.72
6P	19.8	23.76
5P	15.84	19.8
4P	11.88	15.84
3P	7.92	11.88
2P	3.96	7.92
NUMBER OF PINS	DIM. A	DIM. B

9396WV-XXP	Nylon 66 UL94V-0	9396H	9396T
PART NO	Material	Suitable Housing	Suitable Terminal

2	PIN	n PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:本色
NO.	NAME	Q'TY	DESCRIPTION

new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	9396WV-XXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25
			MODEL NAME	H-9396WV-XXP		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD			X.xx
FILE NO.							