



Specifications:
 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:500V
 AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-40℃-+85℃
 温度范围: -40℃-+85℃
 Insulation resistance:100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance:20mΩ Max
 接触电阻: 20mΩ Max

X1011 H - 2xXX- N0 HF
 ① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-HSG
- 3.Row No.Pin No:2x05~2x25
- 4.Material:N0-Nylon66 (White) UL 94V-0
- 5:HF-Halogen Free

Poles	Dimensions/mm	
	A	B
2x05	4.00	8.00
2x06	5.00	9.00
2x08	7.00	11.00
2x09	8.00	12.00
2x10	9.00	13.00
2x15	14.00	18.00
2x20	19.00	23.00
2x25	24.00	28.00

X1011H-2xXX-N0HF	Nylon66	X1011W	X1011T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1011H-2xXX-N0HF
CHKD		UNIT: mm/in	DWG NO.: X-X1011H-2xXX-N0HF
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

广东星坤科技股份有限公司

DATE	日期
DESCRIPTION	文件工程章

REVISIONS	DATE	REVISED	APPROVED	ANGLAR	±5°
				L ≤ 4	±0.2
				4 < L ≤ 16	±0.3
				16 < L ≤ 63	±0.4
				L > 63	±0.5
				UNSPECIFIED TOLERANCES	