

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀金1u"

Contact: bronze, 1u" GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C

Ordering Information

F159-12 20 A1 B SU C 2

NO. OF PINS
PER ROW
2-40P

Contact
Full of Gold

Plating
Semi-gold



INSULATOR
MATERIAL:

PACKING
A: PE Bag
B: Tape & Peel
C: Tube
D: Tube+CAP
E: Tray

A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

B0=0.8U"
B1=1U"
B2=1.5U"
B3=2U"
B4=3U"
B5=5U"
B6=10U"
B7=15U"
B8=20U"
B9=30U"

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature



			OPERATION		SCALE		Fit		东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.	
			X.X	+0.40	UNIT		MM			
			X.XX	+0.25	SIZE	A4	DESIGN	秦星宇 2020.05.14	PART NO.	F159-1220A1BSUC2
			X.XXX	+0.15	SHEET	1/1	CHECK		TITLE:	2.54mm排母 塑高5.9mm 2*20P 180度 DIP:3.1 侧插式 PA6T料 镀金1u" 管装 K2969
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		PROJ.	APPROVE			Customer No.	