

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色:黑色.

Housing:PBT+30%G.F UL94V-0, Color:Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact:Bronze, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40° C to+105° C

Temperture Range: -40° C to+105° C



Ordering Information

F185-11 06 A0 A SU C 2

NO OF PINS
PER ROW
1-40P

Contact
Full Cf Gold

Plating
Semi-gold

INSULATOR
MATERIAL:

PACKING
A: PE Bag

A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

B0=0.8U"
B1=1U"
B2=1.5U"
B3=2U"
B4=3U"
B5=5U"
B6=10U"
B7=15U"
B8=20U"
B9=30U"

A: PBT
B: PA6T
C: PA9T
D: LCP

B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

RoHS
COMPLIANT

客编: K8002

注意
事项

1. 带*为品质重点
点检验尺寸

			OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司		
			X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
			X.XX	±0.20	SIZE	A4	DESIGN	李官森2022.04.03	PART NO. F185-1106A0ASUC2		
			X.XXX	±0.10	SHEET	1/1	CHECK		TITLE: FH2.54*8.5 1*6P 180度 切脚DIP: 2.3 塑宽 =3.0mm 0型A款 PBT料 镀普金		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		PROJ.	APPROVE			Customer No.		
A0	2022.04.03	/	新版发行								