

# Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: LCP+30%G.F UL94V-0, 颜色: 黑色.  
 Housing: LCP+30%G.F UL94V-0, Color: Black  
 端子: 青铜, 镍底30u"MIN, 表面镀金1u"MIN  
 Contact: Bronze, 1u"MIN GOLD PLATING OVER ALL  
 30u" MIN NICKEL UNDERPLATING OVER ALL



2. 特性 (characteristics):

额定电流: 7 AMP  
 Rating Current: 7 AMP.  
 接触阻抗: 20 mΩ MAX.  
 Contact Resistance: 20 mΩ MAX.  
 绝缘阻抗: 1000 MΩ MIN.  
 Insulating Resistance: 1000 MΩ MIN.  
 耐电压: AC 500V.  
 Withstanding Voltage: AC 500V.  
 温度范围: -40° C to +105° C  
 Temperature Range: -40° C to +105° C

# Ordering Information

F789-11 04 A0 D SU C 2

NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL	PACKING
1-30P	Full of Gold Semi-gold	PC LCP	A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
A0=0.8u"	B0=0.8u"		
A1=1u"	B1=1u"		
A2=1.5u"	B2=1.5u"		
A3=2u"	B3=2u"		
A4=3u"	B4=3u"		
A5=5u"	B5=5u"		
A6=10u"	B6=10u"		
A7=15u"	B7=15u"		
A8=20u"	B8=20u"		
A9=30u"	B9=30u"		
S1=Q di nary Tin Plated			
S2=Mat te Tin Plated			
S3=Ti n-pl ated High-tem per at ure			



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	OPERATION		SCALE		Fit		DESIGN	PART NO	TITLE	Cust order No.
					X.X	+0.25	UNIT	MM	SIZE	A4				
					X.XX	+0.20	SIZE	A4			杨哲	F789-1104A0DSUC2	3.96mm排母 塑高8.9 1*4P 镀黄金	
					X.XXX	+0.10	SHEET	1/1				LCP料 180度 U型 管装		
					Angle	+13°	PROJ.							
					DI M	TOL								

**Yxcon** 东莞市宇熙精密连接器有限公司  
 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.