



- 1.MATERIAL:  
 HOUSING:HIGH TEMPERATURE THERMOPLASTIC. UL94V-0.  
 HOLDER:BRASS.  
 CONTACT:COPPER ALLOY.
- 2.PLATED:  
 CONTACT: Au PLATING IN CONTACT AREA,Sn IN SOLDER TAILS,  
 Ni UNDERPLATED OVERALL.  
 HOLDER: Ni UNDERPLATED OVER ALL,THE SURFACE IS COATED WITH TIN
- 3.ELECTRICAL SPECIFICATION  
 CURRENT RATING:0.5A  
 VOLTAGE RATING: 500V AC  
 OPERATION TEMPERATURE RANGE: -25 C to +85 C  
 CONTACT RESISTANCE: 100MILLIOHMS MAX.  
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC  
 INSULATION RESISTANCE: 100 MEGOHMS MIN.

HOAUC 深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: XQD全塑卡座
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYC006-XQD21-530B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2304171601
			SHEET NO. 1 OF 1