


PIN Assignment

PIN NO.	Signal
1	GND
2	PERn1
3	PERp1
4	GND
5	PETn1
6	PETp1
7	Reserved
8	Reserved
9	PERST#
10	+3.3V
11	CLKREQ#
12	INS#
13	PEFCLK-
14	PEFCLK+
15	GND
16	PERn0
17	PERp0
18	GND
19	PETn0
20	PETp0
21	GND



NOTES:

- MATERIAL:
 - Housing: Engineering plastic, LCP with G.F reinforced, black per UL 94V-0 rate.
 - Slider: Engineering plastic, LCP with G.F reinforced, black per UL 94V-0 rate.
 - Terminal: Phosphor Bronze, per JIS 5191, 0.2t.
 - Spring: Piano thread.
 - Metal: cover: Stainless steel sheet SUS304, 0.2t.
 - Crank: Stainless rod SUS 304.
 - Card lock: Stainless steel SUS304.
- PLATING: Solder zone: 0.381µm (15µ") gold plating in contact area, 2.54µm (100µ") matte tin, 1.27µm (50µ") min. Nickel underplating over all.
- RoHS: compliant products.
- OPERATING TEMPERATURE: -25° ~ +85° C
- ELECTRONICAL SPECIFICATION:
 - CURRENT: DC 0.5A
 - VOLTAGE: DC 5V
 - D. W. VOLTAGE: AC 500Vrms/min.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: CF EXPRESS HOST CONNECTOR PUSH TYPE
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. : HYCW22-CF21-475B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO. : HYC-2106011839
			SHEET NO. : 1 OF 1