


- SPECIFICATIONS**
1. Current Rating: 2A AC, DC
  2. Voltage Rating: 250V AC, DC
  3. Temperature Range: -25°C~ +85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 1000mΩ Min
  6. Withstanding Voltage: 1000V AC/minute
  7. Material: Wafer Nylon66 UL94-VO(2)  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2AW-R	2.00	6.00
3	XD-HY-3AW-R	4.00	8.00
4	XD-HY-4AW-R	6.00	10.00
5	XD-HY-5AW-R	8.00	12.00
6	XD-HY-6AW-R	10.00	14.00
7	XD-HY-7AW-R	12.00	16.00
8	XD-HY-8AW-R	14.00	18.00
9	XD-HY-9AW-R	16.00	20.00
10	XD-HY-10AW-R	18.00	22.00
11	XD-HY-11AW-R	20.00	24.00
12	XD-HY-12AW-R	22.00	26.00
13	XD-HY-13AW-R	24.00	28.00
14	XD-HY-14AW-R	26.00	30.00
15	XD-HY-15AW-R	28.00	32.00
16	XD-HY-16AW-R	30.00	34.00



GENERAL TOLERANCE			制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	HY (2.00) 单排带扣 弯针 红色	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-HY-NAW-R	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
Angle ±3.0°								
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						