



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XH-2A-B	2.50	7.50
3	XD-XH-3A-B	5.00	10.00
4	XD-XH-4A-B	7.50	12.50
5	XD-XH-5A-B	10.00	15.00
6	XD-XH-6A-B	12.50	17.50
7	XD-XH-7A-B	15.00	20.00
8	XD-XH-8A-B	17.50	22.50
9	XD-XH-9A-B	20.00	25.00
10	XD-XH-10A-B	22.50	27.50
11	XD-XH-11A-B	25.00	30.00
12	XD-XH-12A-B	27.50	32.50
13	XD-XH-13A-B	30.00	35.00
14	XD-XH-14A-B	32.50	37.50
15	XD-XH-15A-B	35.00	40.00
16	XD-XH-16A-B	37.50	42.50

Ordering Information

XD - XH - N *** - * - **

Pin	Type	Colour	Contact Plating
	针型	颜色	镀层
	A=直针	红色	0.1µm Gold
	AH=斜针	蓝色	0.2µm Gold
	AL=20度	黄色	0.3µm Gold
	AH=45度	绿色	0.5µm Gold
		白色	1.0µm Gold
		棕色	2.0µm Gold
		黑色	5.0µm Gold
		灰色	10µm Gold
		银色	20µm Gold

GENERAL TOLERANCE			制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd	产品名称 TITLE	XH (2.50) 单排 直针 黑色	版本 REV.	A
DIM TOL			审核 CHECK			产品料号 PART NO.	XD-XH-NA-B	单位 UNITS	mm
X.X ±0.30			批准 APPROVAL		材料 MATERIAL		页次 SHEET	1/1	
X.XX ±0.20			比例 SCALE						
X.XXX ±0.10			投影 Projection						
Angle ±3.0°									
1	初版发行								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							