



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XH-2AW-L	2.50	7.50
3	XD-XH-3AW-L	5.00	10.00
4	XD-XH-4AW-L	7.50	12.50
5	XD-XH-5AW-L	10.00	15.00
6	XD-XH-6AW-L	12.50	17.50
7	XD-XH-7AW-L	15.00	20.00
8	XD-XH-8AW-L	17.50	22.50
9	XD-XH-9AW-L	20.00	25.00
10	XD-XH-10AW-L	22.50	27.50
11	XD-XH-11AW-L	25.00	30.00
12	XD-XH-12AW-L	27.50	32.50
13	XD-XH-13AW-L	30.00	35.00
14	XD-XH-14AW-L	32.50	37.50
15	XD-XH-15AW-L	35.00	40.00
16	XD-XH-16AW-L	37.50	42.50



GENERAL TOLERANCE			制图 DRAWING	09	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	XH (2.50) 单排 弯针 蓝色	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-XH-NAW-L	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		角度 Angle	±3.0°				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						