



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XH-2A-P	2.50	7.50
3	XD-XH-3A-P	5.00	10.00
4	XD-XH-4A-P	7.50	12.50
5	XD-XH-5A-P	10.00	15.00
6	XD-XH-6A-P	12.50	17.50
7	XD-XH-7A-P	15.00	20.00
8	XD-XH-8A-P	17.50	22.50
9	XD-XH-9A-P	20.00	25.00
10	XD-XH-10A-P	22.50	27.50
11	XD-XH-11A-P	25.00	30.00
12	XD-XH-12A-P	27.50	32.50
13	XD-XH-13A-P	30.00	35.00
14	XD-XH-14A-P	32.50	37.50
15	XD-XH-15A-P	35.00	40.00
16	XD-XH-16A-P	37.50	42.50

Ordering Information

XD - XH - N *** - * - **

Pin	Type	Colour	Contact Plating
	针型	颜色	镀层
	A=直针	和红色	OS/ur Gold
	AH=弯针	绿色	OS/ur Gold
	AL=20度	蓝色	OS/ur Gold
	AH1=带孔	黄色	OS/ur Gold
		白色	OS/ur Gold
		棕色	OS/ur Gold
		灰色	OS/ur Gold
		黑色	OS/ur Gold

GENERAL TOLERANCE			制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd	产品名称 TITLE	XH (2.50) 单排 直针 紫色	版本 REV.	A
DIM TOL			审核 CHECK			产品料号 PART NO.	XD-XH-NA-P	单位 UNITS	mm
X.X ±0.30			批准 APPROVAL		材料 MATERIAL		页次 SHEET	1/1	
X.XX ±0.20			比例 SCALE						
X.XXX ±0.10			投影 Projection						
Angle ±3.0°									
1	初版发行								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							