



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

| Circuit | Part NO. | Dimensions mm | |
|---------|-------------|---------------|-------|
| | | A | B |
| 2 | XD-XH-2A-L | 2.50 | 7.50 |
| 3 | XD-XH-3A-L | 5.00 | 10.00 |
| 4 | XD-XH-4A-L | 7.50 | 12.50 |
| 5 | XD-XH-5A-L | 10.00 | 15.00 |
| 6 | XD-XH-6A-L | 12.50 | 17.50 |
| 7 | XD-XH-7A-L | 15.00 | 20.00 |
| 8 | XD-XH-8A-L | 17.50 | 22.50 |
| 9 | XD-XH-9A-L | 20.00 | 25.00 |
| 10 | XD-XH-10A-L | 22.50 | 27.50 |
| 11 | XD-XH-11A-L | 25.00 | 30.00 |
| 12 | XD-XH-12A-L | 27.50 | 32.50 |
| 13 | XD-XH-13A-L | 30.00 | 35.00 |
| 14 | XD-XH-14A-L | 32.50 | 37.50 |
| 15 | XD-XH-15A-L | 35.00 | 40.00 |
| 16 | XD-XH-16A-L | 37.50 | 42.50 |

Ordering Information

XD - XH - N *** - * - **

| | | | |
|-----|--------|--------|-----------------|
| Pin | Type | Colour | Contact Plating |
| | 针型 | 颜色 | 镀层 |
| | A=直针 | 红色 | OS/ur Gold |
| | AH=弯针 | 蓝色 | OS/ur Gold |
| | AL=20度 | 黄色 | OS/ur Gold |
| | AH1=弯针 | 绿色 | OS/ur Gold |
| | | 白色 | OS/ur Gold |
| | | 棕色 | OS/ur Gold |
| | | 黑色 | OS/ur Gold |

| | | | |
|-------------------|------------|----------|----|
| GENERAL TOLERANCE | | 制图 | 10 |
| DIM TOL | | 审核 | |
| X.X ±0.30 | | 批准 | |
| X.XX ±0.20 | | APPROVAL | |
| X.XXX ±0.10 | | 比例 | |
| Angle ±3.0° | | SCALE | |
| 投影 | Projection | 材料 | |

XD 深圳讯答科技有限公司
ShenzhenXunDaTechnology Co.,Ltd

| | | | |
|------------------|--------------------|-------------|-----|
| 产品名称 TITLE | XH (2.50) 单排 直针 蓝色 | 版本 REV. | A |
| 产品料号 PART NO. | XD-XH-NA-L | 单位 UNITS | mm |
| 材料 MATERIAL | | 页次 SHEET | 1/1 |

| | | |
|-----------|------------------------|-------------------|
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE |
| 1 | 初版发行 | |