



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

| Circuit | Part NO. | Dimensions mm | |
|---------|-------------|---------------|-------|
| | | A | B |
| 2 | XD-XH-2A-V | 2.50 | 7.50 |
| 3 | XD-XH-3A-V | 5.00 | 10.00 |
| 4 | XD-XH-4A-V | 7.50 | 12.50 |
| 5 | XD-XH-5A-V | 10.00 | 15.00 |
| 6 | XD-XH-6A-V | 12.50 | 17.50 |
| 7 | XD-XH-7A-V | 15.00 | 20.00 |
| 8 | XD-XH-8A-V | 17.50 | 22.50 |
| 9 | XD-XH-9A-V | 20.00 | 25.00 |
| 10 | XD-XH-10A-V | 22.50 | 27.50 |
| 11 | XD-XH-11A-V | 25.00 | 30.00 |
| 12 | XD-XH-12A-V | 27.50 | 32.50 |
| 13 | XD-XH-13A-V | 30.00 | 35.00 |
| 14 | XD-XH-14A-V | 32.50 | 37.50 |
| 15 | XD-XH-15A-V | 35.00 | 40.00 |
| 16 | XD-XH-16A-V | 37.50 | 42.50 |

Ordering Information

XD - XH - N *** - * - **

| | | | |
|-----|--------|--------|-----------------|
| Pin | Type | Colour | Contact Plating |
| | 针座 | 颜色 | 镀层 |
| | A=直插 | 红色 | 0.1µm Gold |
| | AH=贴片 | 绿色 | 0.2µm Gold |
| | AL=20脚 | 黄色 | 0.3µm Gold |
| | AW=40脚 | 蓝色 | 0.5µm Gold |
| | | 白色 | 1.0µm Gold |
| | | 棕色 | 2.0µm Gold |
| | | 黑色 | 5.0µm Gold |

| | | | | | | | | | |
|-------------------|------------------------|-------------------|------------------|----|--|------------------|--------------------|-------------|----|
| GENERAL TOLERANCE | | | 制图 DRAWING | 10 | 深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd | 产品名称 TITLE | XH (2.50) 单排 直针 绿色 | 版本 REV. | A |
| DIM TOL | | | 审核 CHECK | | | 产品料号 PART NO. | XD-XH-NA-V | 单位 UNITS | mm |
| X.X ±0.30 | | | 批准 APPROVAL | | 材料 MATERIAL | | 页次 SHEET | 1/1 | |
| X.XX ±0.20 | | | 比例 SCALE | | | | | | |
| X.XXX ±0.10 | | | 投影 Projection | | | | | | |
| Angle ±3.0° | | | | | | | | | |
| 1 | 初版发行 | | | | | | | | |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | | | | | | | |