


| 修订 REV | 标记 MARK | 修改摘要 REVISION DESCRIPTION | 签名 SIGNATURE | 日期 DATE |
|-----------|------------|------------------------------|-----------------|------------|
| AO | | NEW DWG | | 2023-09-25 |




- ◆ SPECIFICATIONS
- Current rating: 2.0A AC, DC
 - Voltage rating: 250V AC, DC
 - Temperature range: -25°C ~ +85°C
 - Insulation resistance: 500MΩ Min.
 - Withstanding voltage: 500V AC/ minute.
 - Contact resistance: 20m Ω Max.

Material:
 Housing: LCP UL94V-0, BEIGE
 Contacts: Brass/ MATTE Sn-plated
 Solder Tabs: Brass/ MATTE Sn-plated
 Suitable: HDGC1508HA-2xXP series Dual Row Housing



| PIN | 尺寸 mm | | |
|-------|-------|-------|-------|
| | A | B | C |
| 2x2P | 1.50 | 3.72 | 6.74 |
| 2x3P | 3.00 | 5.22 | 8.24 |
| 2x4P | 4.50 | 6.72 | 9.74 |
| 2x5P | 6.00 | 8.22 | 11.24 |
| 2x6P | 7.50 | 9.72 | 12.74 |
| 2x7P | 9.00 | 11.22 | 14.24 |
| 2x8P | 10.50 | 12.72 | 15.74 |
| 2x9P | 12.00 | 14.22 | 17.24 |
| 2x10P | 13.50 | 15.72 | 18.74 |
| 2x11P | 15.00 | 17.22 | 20.24 |
| 2x12P | 16.50 | 18.72 | 21.74 |
| 2x13P | 18.00 | 20.22 | 23.24 |
| 2x14P | 19.50 | 21.72 | 24.74 |
| 2x15P | 21.00 | 23.22 | 26.24 |
| 2x16P | 22.50 | 24.72 | 27.74 |
| 2x17P | 24.00 | 26.22 | 29.24 |
| 2x18P | 25.50 | 27.72 | 30.74 |
| 2x19P | 27.00 | 29.22 | 32.24 |
| 2x20P | 28.50 | 30.72 | 33.74 |

SECTION A-A

P.C.B LAYOUT
 TOLERANCE: ±0.05



深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co., LTD
 电话: 0755-27129737 传真: 0755-29940187

| -TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表 | |   | | TITLE: 产品名称: HDGC1.5带扣立贴 | | | | |
|---|-------|---|-------|-----------------------------|--------------------------------------|-------|------|-------------|
| X.X | ±0.15 | X.X* | ±3' | APPD: 核准: 谢亮 | PART NO: 产品编号: HDGC1508WVA-S-2xXP | | | |
| X.XX | ±0.05 | X.XX* | ±1' | CHECK: 校对: 王建业 | DATE | SCALE | UNIT | CODE NUMBER |
| X.XXX | ±0.03 | X.XXX* | ±0.5' | DRAW: 绘图: 黄艳兰 | 2023-09-25 | 1:1 | mm | A001 |