


**SPECIFICATIONS**

- 1.Voltage rating: 50V AC, DC
- 2.Current rating: 1A, AC, DC
- 3.Withstanding Voltage: 500V AC/minute
- 4.Insulation resistance:100M min
- 5.Temperature range: -25 ° C-+85 ° C
- 6.Contact resistance: 30m max


**TERMINAL**

Material:Phosphor Bronze  
 Finish: Plated Tin or Plated Gold  
 Applicable wire: AWG#26-#30  
 Used in :P1257 SERIES HOUSING  
 Qty/Reel: 20000PCS  
 Part No.: T1257PS-2


00=镀金 2=镀锡




SECTION: A-A  
SCALE: 1:1



SECTION: B-B  
SCALE: 1:1



SECTION: C-C  
SCALE: 1:1



WWW.XFCN.COM

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30 X° ±5°	CHKD				DATE	2010. 4. 12
				.X	±0.20 .X° ±2°	APPD		PRODUCT NAME	1.25mm Crimp Style Connectors	UNITS	mm
				.XX	±0.08 .XX° ±1°	VIEW	⊕	PART. NO.	T1257PS-2	SCALE	1:1
				.XXX	±0.03 .XXX° ±0.5°			DWG. NO.	009		
A0	MODIFICATION	DRAW	DATE								