



SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
- 2.Current rating: 5A, AC, DC
- 3.Withstanding Voltage: 1500V AC/minute
- 4.Insulation resistance:1000M min
- 5.Temperature range: -25 ° C~+85 ° C
- 6.Contact resistance: 20m max


TERMINAL

Material:Phosphor Bronze or Brass
 Finish: Plated Tin or Plated Gold
 Applicable wire: AWG#22-#26
 Used in :P2553 SERIES HOUSING
 Qty/Reel: 15000PCS
 Part No.: T2553BS-xx


00=镀金 2=镀锡



SECTION: A-A



SECTION: B-B



SECTION: C-C

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	2.54mm Crimp Style Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	SCALE	1:1
				.XXX	±0.03	.XXX°	±0.5°			DWG. NO.	009
AO	MODIFICATION		DRAW	DATE							