



SPECIFICATIONS
 Rated Current:3.0AMP
 Contact Resistance:20mΩMax
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩMin
 Operation Temperature:-40°c to +105°c

Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester(UL94V-0)
 Standard: PA66
 Max.Processing Temp: 180°C for 30-60 seconds
 (230°C for 10 seconds)

Ordering Information

HC-JP 254 - 1 - ** - OP - * - **

No.of Rows 1=Single Type	Length (mm) 45=4.5mm 60=6.0mm 65=6.5mm 135=13.5mm	Type OP=Open CL=Close	Color B=Black L=Blue R=Red W=White Y=Yellow V=Green	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
-----------------------------	--	-----------------------------	---	--

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.54 跳线帽 蓝色 (开口 加长带柄)	版本 REV.	A	
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-JP254-1-135-OP-L-G1	单位 UNITS	mm	
			X.XXX ±0.10	投影 Projection	材料 MATERIAL				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					页次 SHEET	1/1