


注記 NOTES

- 材料 MATERIAL
ウエハー PBT (ガラス 15% 入り)
WAFER G.F. 15%
UL94V-0
ピン : 黄銅, 錫メッキ
PIN : BRASS, TIN
- 嵌合相手 : 52418 シリ - ズ
MATE WITH : 52418 SERIES
- △ キンクは全ピンに交互に付加。
SET KINK ALTERNATELY TO ALL PIN.
- 各部のソリは 0.2MAX.
CAMBER : 0.2MAX.
- 本製品は、53290-**10 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 53290-**10.
- 梱包仕様 PACKAGING
53290-**8* トレー TRAY
53290-**4* ポリ袋 POLYBAG

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
10 ^{UNDER}	±0.2	DIMENSION UNITS	SCALE		
10 ^{OVER} 30 ^{UNDER}	±0.25	mm	NTS	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#511689.	
30 ^{OVER}	±0.3	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 745492	
ANGULAR ±3°		ANGULAR TOL	± 3.0°	DRWN: LIKITV	2023/04/25
		4 PLACES	± 0.2	CHK'D: GGA	2023/05/25
		3 PLACES	± 0.25	APPR: GGA	2023/05/25
		2 PLACES	± 0.3	INITIAL REVISION:	
		1 PLACE	±	DRWN: JSASAMOR	2004/09/14
		0 PLACES	±	APPR: NUKITA	2004/09/24
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING
					A3-SIZE
				SERIES	53290
				MATERIAL NUMBER	SEE TABLE
				CUSTOMER	GENERAL MARKET
				DOCUMENT NUMBER	SD-53290-004
				DOC TYPE	PSD
				DOC PART	001
				REVISION	B1
				SHEET NUMBER	
				1 OF 2	



43	41.64	38	53290 - 2080	20
39	37.64	34	- 1880	18
37	35.64	32	- 1780	17
35	33.64	30	- 1680	16
33	31.64	28	- 1580	15
31	29.64	26	- 1480	14
29	27.64	24	- 1380	13
27	25.64	22	- 1280	12
25	23.64	20	- 1180	11
23	21.64	18	- 1080	10
21	19.64	16	- 0980	9
19	17.64	14	- 0880	8
17	15.64	12	- 0780	7
15	13.64	10	- 0680	6
13	11.64	8	- 0580	5
11	9.64	6	- 0480	4
9	7.64	4	53290 - 0380	3
C	B	A	MATERIAL NO. COLOR : NATURAL(WHITE) 色 : ナチュラル (白)	極数 CKT.

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
		DIMENSION UNITS	SCALE					CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#511689.						
10 ^{UNDER}	±0.2	mm	NTS	EC NO: 745492 DRWN: LIKITV 2023/04/25 CHK'D: GGA 2023/05/25 APPR: GGA 2023/05/25 INITIAL REVISION: DRWN: JSASAMOR 2004/09/14 APPR: NUKITA 2004/09/24				2.0 BOARD TO BOARD CONN. WAFER ASS'Y - LEAD FREE-						
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 3.0°						PRODUCT CUSTOMER DRAWING						
10 ^{OVER} 30 ^{UNDER}	±0.25	4 PLACES ± 0.2						DOCUMENT NUMBER				DOC TYPE	DOC PART	REVISION
30 ^{OVER}	±0.3	3 PLACES ± 0.25						SD-53290-004				PSD	001	B1
ANGULAR ±3°		2 PLACES ± 0.3						MATERIAL NUMBER				CUSTOMER		SHEET NUMBER
		1 PLACE ±		SEE TABLE				GENERAL MARKET		2 OF 2				
		0 PLACES ±		DRAWING										
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		SERIES								
				A3-SIZE		53290								

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/25	09:42:59
-----------------	----	--------------	------------	----------