


PZB300MC23R30

Aliases (P300PL154M275AC472)

PZB300/P300, Film, Metallized Paper, Safety, 0.15 uF, 20%, 100°C, Lead Spacing = 20mm



Note: '()' correspond to the letters used in the product bulletin Click here for the 3D model.

Dimensions	
L	24mm MAX
Н	16mm MAX
т	12.5mm MAX
S	20mm +/-0.5mm
S1	10mm NOM
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications			
Packaging	Bulk, Bag		
Packaging Quantity	150		

General Information	
Series	PZB300/P300
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	3 Leads
Safety Class	Delta EMI X2+Y2+Y2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Construction	Molded
Typical Component Weight	6.75 g
Miscellaneous	y2_cap_value= 0.0047 uF.

Specifications			
0.15 uF			
20%			
275 VAC			
-40/+100°C			
100°C			
1.3% 1kHz			
12 GOhms			
600 V/us			

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.