

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484 EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

CT25E-16T150-1

Former P/N: CEMT250B125-12C15PLR / CEMT250B-12PLR

Rev. 7-2023 RoHS3 & REACH Electromagnetic Sound Transducers




Operating Characteristics

ELEC	TRICAL	
	Rated Voltage	12.0 Vo-p
	Operating Voltage	8.0 to 16.0 Vo-p
	Coil Resistance	120 ± 12 Ω

Max Current at V Rated 55 mA

ACOUSTIC



Physical Characteristics

MATERIAL Housing


Housing	Noryl
Diaphragm	Ni-alloy
PC Pin	Tin Plated Brass

TEMPERATURE RANGES

Operating -40 to +85 °C
Storage -40 to +85 °C

Weight 10 g

Tolerance: ± 0.5mm unless specified otherwise.



All measurements in mm unless otherwise noted.

Revision	Description	Ву	Date
6-2020	Added abbreviated former PN. Added general tolerance.	JL	2020-11-03
7-2023	Added part image.	SK	2023-05-08

Warranty: For a period of two (2) years from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.