


			1		
	Part Number:	3409-1	DRAWN	E (4.5 (204.5	
	TD202		CJ	5/16/2016	
	17293		CHECKED	5/18/2016	
			P.D.		
	Description:	ansducer	APPROVED	5/18/2016	
	Plezo 116		J.S.		


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View


Weight



Side View



Bottom View



Items	Specifications	Conditions						
Sound Pressure Leve	el 109	dB (@ 10cm)						
Resonant Frequency	3,400	Hz		REVISION HISTORY				
Rated Voltage	9	V	REV	DESCRIPTION	DATE	APPROVED		
Voltage Range	9 ~ 28	V		Released from Engineering	10/21/2013	J.S.		
Capacitance	25,000	pF (@ 120 Hz)	1	Updated to new template	5/18/2016	J.S.		
Max. Rated Current	180	mA	2	Corrected SPL	5/18/2017	C.E.		
Storage Temperature	e -30 ~ +70	°C		NOTES				
Operating Temperatu	re -20 ∼ +60	°C		All dimensions are in mm unless otherwise noted				
Connection Method	Lead Wires			2) All tolerances are ± 0.5 mm unless otherwise noted				
Mount Type	Flush Mount			3) All parts meet RoHS				
Housing Material	ABS			4) Subject to change or redrawn without notice				