



		<u>T</u>	
Part Number:		DRAWN	
TE024	1003-1	CJ	11/12/2019
IEU34		CHECKED	11/12/2019
		J.S.	11/12/2019
Description:		APPROVED	11/12/2010
Electro-Mechani	nical Transducer	C.F.	11/12/2019

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Items	Specifications	Conditions							
Min. Sound Pressure Level	>64	dB (@ 10cm)							
Resonant Frequency	4,000	Hz							
Rated Voltage	3	V							
Voltage Range	2 ~ 4	V	REVISION HISTORY						
Coil Resistance	12	Ω	REV	DESCRIPTION	DATE	APPROVED			
Max. Rated Current	120	mA		Released from Engineering	11/12/2019	J.S.			
Storage Temperature	-30 ~ +80	°C	NOTES						
Operating Temperature	-20 ~ +70	°C	1) All dimensions are in mm unless otherwise noted						
Connection Method	Surface Mount Pads			2) All tolerances are ± 0.3 mm unless otherwise noted					
Mount Type	Surface Mount			3) All parts meet RoHS					
Housing Material	LCP			4) Subject to change or redrawn without notice					
Weight	0.1	g							
vveignt	0.1	9		2	T				